


Device Specification

MDFG1-0.5-xx

version 2.1/2010



[Image for reference only. Not to scale.]

Description MgO doped PPLN DFG crystal for 1064nm and 737-786nm
Thickness(z) $0.5\text{mm} \pm 0.05\text{mm}$
Width(y) $10\text{mm} \pm 0.5\text{mm}$
Length(x) $40\text{mm} \pm 0.5\text{mm}$ or $20\text{mm} \pm 0.5\text{mm}$
Periods(Λ) 18.50, 18.80, 19.10, 19.40, 19.70, 20.00, 20.30, 20.60, 20.90 μm

NOTES:



- 1 The DFG device material is Magnesium doped Lithium Niobate with nine periodically poled gratings. Each grating is 0.5mm wide with individual periods as listed above. A saw-cut reference mark is provided on the +z face of the crystal to determine the largest grating period (see above diagram). Each poled grating is separated by 0.2mm wide regions of unpoled material.
- 2 The average mark-to-space ratio of each grating is better than 70:30.
- 3 Each device is etched to make the poled gratings visible. Due to the wet-etch nature of this process the top and bottom surface finish of each device may appear cloudy or uneven.
- 4 Perpendicularity of input/output facets F1 and F2 to gratings is within $\pm 0.15^\circ$. Parallelism between end facets F1 and F2 is within ± 5 minutes.
- 5 Optical finish of facets F1 and F2 is within 20/10 scratch dig with $\lambda/8@1064\text{nm}$. No more than two 100 μm size chips per end facet.
- 6 AR coated to $R < 1.5\%$ @ 700-1100nm for the input facet (F2) and 2.4-4.8 μm for the output facet (F1).

Device Specification

MDFG1-0.5-xx

version 2.1/2010

DFG Tuning Curve for 1064nm Pump



For more information, please contact us at:

tel: +44 (0)1794 521 638

fax: +44 (0)8709 289 714

email: sales@covesion.com

www.covesion.com

Covesion Ltd. Unit A7, The Premier Centre, Premier Way, Romsey, SO51 9DG, UK

Registered in England No. 06338847, VAT No. 943 1896 00

Copyright © 2010 Covesion Ltd.

